

Rozvodnica zapustená UK600, IP 30, plechové plné dvere

Kód produktu 2CPX077840R9999

Typové číslo UK612E2

Variant 12 M



POPIS

Stupeň krytia: IP 30



12 modulov (12 × 1), vrátane svorkovnic N a PE.

Plechové plné dvierka.

Farba: biela RAL 9016

Rozmery (š × v × h): 355 × 367 × 95 mm

ĎALŠIE VARIANTY

Variant	Kód produktu
 24 M	2CPX077841R9999
 36 M	2CPX077842R9999
 48 M	2CPX077843R9999
 60 M	2CPX077844R9999
 3 Radv	2CPX031387R9999
 4 Radv	2CPX031388R9999
 5 Radov	2CPX031389R9999
 3 Radv	2CPX031384R9999
 4 Radv	2CPX031385R9999
5 Radov	2CPX031386R9999