

# Rozvodnica zapustená UK600, IP 30, plechové plné dvere

**Kód produktu** 2CPX077840R9999

**Typové číslo** UK612E2

**Variant** 12 M



## POPIS

Stupeň krytia: IP 30











12 modulov (12 × 1), vrátane svorkovnic N a PE.

Plechové plné dvierka.

Farba: biela RAL 9016

Rozmery (š × v × h): 355 × 367 × 95 mm

## ĎALŠIE VARIANTY

	Variant	Kód produktu
	24 M	2CPX077841R9999
	36 M	2CPX077842R9999
	48 M	2CPX077843R9999
	60 M	2CPX077844R9999
	3 rady	2CPX031387R9999
	4 rady	2CPX031388R9999
	5 radov	2CPX031389R9999
	3 rady	2CPX031384R9999
	4 rady	2CPX031385R9999
	5 radov	2CPX031386R9999