

Rozvodnica multimediálna zapustená UK600, IP 30, plechové dvierka s vetracími otvormi

Kód produktu 2CPX031384R9999

Typové číslo UK636MV

Variant 3 rady



POPIS

3 montážne rady

Plechová dvierka s vetracími otvory

Stupeň krytia: IP 30

Farba: biela RAL 9016

Rozmery (š × v × h): 605 × 367 × 95 mm

ĎALŠIE VARIANTY

Variant	Kód produktu
 12 M	2CPX077840R9999
 24 M	2CPX077841R9999
 36 M	2CPX077842R9999
 48 M	2CPX077843R9999
 60 M	2CPX077844R9999
 3 Rady	2CPX031387R9999
 4 Rady	2CPX031388R9999
 5 Radov	2CPX031389R9999
 4 Rady	2CPX031385R9999
5 Radov	2CPX031386R9999