

Rozvodnica multimediálna zapustená UK600, IP 30, plechové dvierka s vetracími otvormi a vložkou pre WiFi - Kópia

Kód produktu 2CPX031389R9999

Typové číslo UK660MW

Variants 5 radov



POPIS

5 montážnych radov










Plechová dvierka s vetracími otvory

Stupeň krytia: IP 30

Farba: biela RAL 9016

Rozměry (š × v × h): 855 × 367 × 95 mm

ĎALŠIE VARIANTY

Variants	Kód produktu
 12 M	2CPX077840R9999
 24 M	2CPX077841R9999
 36 M	2CPX077842R9999
 48 M	2CPX077843R9999
 60 M	2CPX077844R9999
 3 Rady	2CPX031387R9999
 4 Rady	2CPX031388R9999
 3 Rady	2CPX031384R9999
 4 Rady	2CPX031385R9999
5 Radov	2CPX031386R9999